



Power supplies for spectral lamps

In applications of spectroscopy special light sources as deuterium lamps, mercury lamps, Xenon lamps or hollow cathode lamps are used. For these kind of gas discharge lamps or also known as arc lamps DURATEC offers a wide range of power supplies which can be customized to special requirements. In standard analytical systems the anode current of the lamp is DC controlled to a constant value. For radiation purposes the more simple AC mode is mostly sufficient.

- wide range of power supplies
- AC or DC controlled
- flexible design

Power supplies

Power supply for 30W deuterium lamps DC controlled anode	792 000
Power supply for 200W deuterium lamps Heraeus D-200 and D-200F	792 020
Power supply for mercury lamps of Heraeus' ST-series	792 005
Power supply for NK lamps of Heraeus' NK-series (AC mode)	792 011
Power supply for diving lamp Heraeus TQ150	792 010
Power supply for hollow cathode lamps	792 060



Rheinauer Str. 4 · D-68766 Hockenheim
 Tel. 0 62 05 / 94 50-0
 Fax 0 62 05 / 94 50-33
 info@duratec.de
 www.duratec.com

- Please send an offer
- Please call me
Phone
- Please make date for demonstration

.....
 Company


.....
 Name

.....
 Department

.....
 Address

.....
 City and Zip-Code

.....
 eMail



DURATEC
 ANALYSENTECHNIK GMBH

Rheinauer Strasse 4

D-68766 Hockenheim
 GERMANY